



Spark



## FORM ADDS FUNCTION

The unique contour of the Spark's backrest increases the usable depth of the seating system by allowing the seat to move underneath the back by an extra 2". This innovative design also comes with 32° of built-in angle-adjustability and the ability to change the depth by 4", in 1" increments.



## SIMPLICITY IS CATCHING

With a clean, ergonomic, easy-to-release latch, the chair folds into an incredibly small package and opens again with a snap! Spark uses an aesthetically pleasing frame extender keeping the length of the frame shorter and stronger and making the chair more manageable for the user and caretaker.



## DIRECT MOUNT HANGERS

Our new 70°, 80° and 90° hangers have been redesigned to allow for very short leg lengths. With a minimum footrest length of 3 3/4" and adjustments in 1/2" increments, the best hanger in the industry now works great for kids!



# A UNIQUE PEDIATRIC WHEELCHAIR

*Spark is designed to be used with virtually any clinically prescribed seating system.*

## SPECIFICATIONS

Transport Weight:	17.5 lbs.*	7.94 kg*
Seat Width:	10-16 in.	25-41 cm
Seat Depth:	12-18 in.	31-46 cm
Front Seat Height:	13-21 in.	33-53 cm
Rear Seat Height:	11-18.5 in.	28-47 cm
Top Tubing Size:	1 in.	2.54 cm
Bottom Tubing Size:	1 in.	2.54 cm
Weight Capacity:	168 lbs.	76 kg
Ansi Resna WC-19 Transit:	Yes	Yes

\* 12"x12" Frame with Stroller Handle Back Posts, and 5" Poly Casters. Armrests, Footrest and Rear Wheels removed.